

Specifications

Photo is representative

Eaton MIC-6

Eaton Bussmann series MIC fuse, Fast acting, Midget fuse, Control circuits, PLC circuits, Electronic circuits, 6 A, Non-indicating, 200 AIC at 250 Vac, Nickel-plated bronze endcap, Fiber tube, Standard, 250 V

General specifications

PRODUCT NAME	Eaton Bussmann series MIC fuse
CATALOG NUMBER	MIC-6
UPC	051712183932
PRODUCT LENGTH/DEPTH	1.813 in
PRODUCT HEIGHT	0.47 in
PRODUCT WIDTH	0.47 in
PRODUCT WEIGHT	1.5 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked
PRODUCT TYPE	Fuse

Electrical rating

AMPERAGE RATING	6 A
INTERRUPT RATING	200 AIC at 250 Vac
VOLTAGE RATING	250 V

General information

FUSE INDICATOR	Non-indicating
----------------	----------------

Physical details

MATERIAL	Fiber tube Nickel-plated bronze endcap
PACKAGING TYPE	Standard

Resources

[MIC-6~BUSS MIDGET FUSE](#)

CATALOGS [Bussmann series
complete full line catalog
no. 1007](#)

SPECIFICATIONS AND
DATASHEETS [Eaton Specification Sheet -
MIC-6](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

