Part Number: 98463-1510

Image not available

Series image - Reference only

Status: Active - Custom
Series: 98463
Category: Molex Parts

Go to Part Detail

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU RoHS: ELV and RoHS Compliant
China RoHS:
REACH SVHC: Not Reviewed
Low-Halogen Status: Not Low-Halogen

Product Compliance Statement

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part

Part Detail

COLLAPSE ALL

General

Status	Active - Custom
Category	Molex Parts
Series	98463
UPC	800756618043

Physical

Net Weight	15.335/g

Solder Process Data

Duration at Max. Process Temperature (seconds)	25
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260

Material Info

Copyright 2015

Downloaded from Arrow.com.