

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.


LOC	DIST
DY	-

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	O4	REVISED PER ECO-09-026495	28NOV09	KK	AEG









DETAIL A
(SCALE 4-1)





DETAIL B



NOTES:

1. MATERIAL:
   HOUSING: HIGH TEMP THERMOPLASTICS UL94-V0
   CONACTS: COPPER ALLOY
2. FINISH:
   UNDERPLATE: 1.3um MIN NICKEL
   MATING AREA: 0.2um MIN Au
   SOLDERTAIL: 2.0um MIN MATTE TIN
3. FINISH:
   UNDERPLATE: 1.3um MIN NICKEL
   MATING AREA: 0.76um MIN Au
   SOLDERTAIL: 2.0um MIN MATTE TIN
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

REMARKS	QTY	HEIGHT TYPE	G	F	E	D	C	B	A	CONNECTOR P/N	POS	PART NO.
3	200	13H	300	25.8	16	21.8	44	40.4	20.2	5-6123212-1	40	2-5084968-1
2	200	13H	300	57.8	16	53.8	72	68.4	34.2	5-5179010-5	120	0-5084968-5
2	200	13H	300	49.8	16	45.8	72	68.4	34.2	5-5179010-4	100	0-5084968-4
4	200	13H	300	33.8	16	29.8	44	40.4	20.2	5-5179010-2	60	~~0-5084968-2~~
	200	13H	300	25.8	16	21.8	44	40.4	20.2	5-5179010-1	40	0-5084968-1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.3
2 PLC ±0.25
3 PLC ±0.2
4 PLC ±-
ANGLES ±3°

MATERIAL 1
FINISH 2 3

DWN YJ SEE 16SEP2005
CHK SF LEONG
APVD SF LEONG
PRODUCT SPEC 108-5390
APPLICATION SPEC 114-5254
WEIGHT -

tyco Electronics
Tyco Electronics Singapore Pte. Ltd.

NAME RECEPTACLE ASSY (0.5 BOSS LENGTH, 13mm HEIGHT, LF) WITH POLYMIDE FILM FOR FH 0.8 B-T-B CONN. ON TAPING

SIZE	CAGE CODE	DRAWING NO
A3	00779	C-5084968

CUSTOMER DRAWING

SCALE	SHEET	REV
2:1	1 OF 1	O4

Downloaded from Arrow.com.