

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
MINNEAPOLIS, MINN.

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-1R95-A21

BZ-1R95-A21

PAGE 1 OF 1

M

DRAWING
NUMBER

ISSUE
7

REPLACES

SR 8921

RELEASE NO.

14 APR 60

RP

CHECK

28 MAR 60

DES

CHECK

30 MAR 94

E C093346

DLT
4 SEP 98

F C093774

JAF
7 JAN 99


CHECK

26 MAR 60

L S D

FORMTEK

0-50378



6-32 NC THREAD, .172 MM
DEPTH, IN INSERTS FOR
TERMINAL CONNECTION (3)

NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 - 6-32 UNC X .219 REF BINDING HEAD COMBINATION TERMINAL SCREW (3)
FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 7-10 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 4 OZ MIN	UL LISTED - FILE E12252 CODE L103 15A-125, 250 OR 480 VAC 1/8HP-125 VAC; 1/4HP-250 VAC	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL ----- .001 MAX	L288 L299 L306	TOLERANCES ARE:
OVERTRAVEL ----- .005 MIN	CE D SP 16A 250V ~ T85 5E4	ONE PLACE (.0) ±.000 TWO PLACE (.00) ±.010 THREE PLACE (.000) ±.000 ANGLES ±
		WEIGHT