

[Home](#)> [5977722607F](#)

Search For

enter search text

Part Number

Part Number: **5977722607F**

| General Description |                          |
|---------------------|--------------------------|
| Series              | 597                      |
| Configuration       | 1210 Package             |
| Description         | SMD LED 1210 Y/G 7" Reel |
| Package Options     | Tape and Reel            |
| Lamp Type           | Bi- Color                |
| Lens Color          | Non - Diffused           |

| Absolute Maximum Ratings (Ta = 25Â° ) |                 |
|---------------------------------------|-----------------|
| Solder Temperature                    | 260Â° for 5 sec |
| Operating Temperature                 | -55~+85         |
| Storage Temperature                   | -55~+85         |

| Operating Characteristics   |        |       |
|-----------------------------|--------|-------|
|                             |        |       |
| Color                       | Yellow | Green |
| Luminous Intensity Min      | 4      | 8     |
| Luminous Intensity Typical  | 9      | 15    |
| Luminous Intensity Max      | 30     | 30    |
| Dominant Wavelength Typical | 588nm  | 569nm |
| Power Dissipation Max       | 60mW   | 100mW |



5977722607F

check stock



[This is a  
RoHS Compliant Product  
To learn more click here](#)