


© 2025 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED AS PER ECN-25-351332	28OCT2025	PSK	J.M





Suggested PCB Footprint



Note: Remove all sharp edges, burrs & pip

ENVIRONMENTAL PARAMETER	
TEMPERATURE RANGE	-55 ℃~+125 ℃

MATERIALS AND PLATING UNIT: MICRO-INCHES	
MATERIALS	PLATING
BRASS ALLOY	GOLD10u"/NICKEL 50u"

TC PN	DIM A	TE DESCRIPTION
2511417-1	0.64	CONTACT PAD, 1.98D X 0.64H, GOLD
2511417-2	1.14	CONTACT PAD, 1.98D X 1.14H, GOLD
2511417-3	1.40	CONTACT PAD, 1.98D X 1.40H, GOLD

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± 0.2
2 PLC	± 0.1
3 PLC	± 0.05
4 PLC	± –
ANGLES	± –

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DWN	PRATHAP SK	20JUN2025
CHK	MADHAN S	20JUN2025
APVD	JAGRUTI	20JUN2025
PRODUCT SPEC	108-162165	
APPLICATION SPEC	–	
WEIGHT	0	
CUSTOMER DRAWING		

TE Connectivity Ltd.

NAME: – CONTACT PAD 1.98D, GOLD –

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2511417	–

SCALE	SHEET	REV
1:1	1 OF 2	A1

2511417

1471-9 (1/15)


Downloaded from Arrow.com.

© 2025 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—

NOTES :
1.PRIMARY PACKING: 2500 PCS/DISH(2500PCS)

2.OUTER PACKING: 4 DISH/CARTON(10000PCS)



4 dish



THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN PRATHAP SK 20JUN2025	TE Connectivity Ltd.	
DIMENSIONS: mm	CHK MADHAN S 20JUN2025	NAME – CONTACT PAD 1.98D, GOLD –	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± – 4 PLC ± – ANGLES ± –	APVD JAGRUTI 20JUN2025	SIZE A2 / CAGE CODE 00779 / DRAWING NO C-2511417	RESTRICTED TO —
MATERIAL –	PRODUCT SPEC 108-162165		
FINISH –	APPLICATION SPEC —		
	WEIGHT —	CUSTOMER DRAWING	SCALE 1:1 / SHEET 2 OF 2 / REV A1

2511417

1471-9 (1/15)

Downloaded from Arrow.com