



Representative Image

Catalog No. RANY-530-9-D

Description: CABLE CLIP ROUND NAT NYL .622IN HGT

UPC No 728494123721

Home > Wire & Cable Management > Ty-Rap > Nylon Cable Clips

Cable Clamp for Round Cables, Natural Polyamide (Nylon 6.6) for Temperatures up to 65 Degrees Celsius (149 F), Length of 25.4mm (1 Inch), Width of 25.4mm (1 Inch), Height of 15.8mm (0.622 Inch), Self-Adhesive Mounting Method

Descriptors

|                  |  |
|------------------|--|
| Category         | Nylon Cable Clips                              |
| Special Features | Versatile adhesive clips keep paths organized. |

Specifications

|          |                       |
|----------|-----------------------|
| Material | Nylon/Polyamide 6.6   |
| Color    | Natural               |
| Mounting | Rubber-Based Adhesive |

Classifications

|            |           |
|------------|-----------|
| Brand Name | Ty-Rap    |
| Sub Brand  | Catamount |

Compliance and Certifications

|       |                             |
|-------|-----------------------------|
| RoHS  | RoHS3 Compliant             |
| REACH | REACH 247 Compliant         |
| TSCA  | TSCA Section 6(h) Compliant |

|                          |  |
|--------------------------|--|
| ETIM                     | EC000449 Mounting base and -element for cable ties |
| Length                   | 25.4 mm  |
| Length                   | 1 inch   |
| Width                    | 25.4 mm  |
| Width                    | 1 inch   |
| Height                   | 15.8 mm  |
| Height                   | 0.62 inch  |
| For max. bundle diameter | 13.46 mm   |
| Type of fastening        | Self-adhesive                                      |
| Material                 | Plastic  |
| Material quality         | Polyamide (PA)                                     |

by ABB

|                     |  |
|---------------------|--|
| ETIM                | EC000449 Mounting base and -element for cable ties |
| Working temperature | 0-+66 °C   |
| Working temperature | 32-+150 °F   |
| Colour              | Natural colour                                     |