

MPA-NCNC440034F-SS



MPO Trunk Cable, polarity A, 48 fiber (4x12), OFNP 3 mm, OM4, 34 ft, with 36" breakouts

OBSOLETE

This product was discontinued on: July 24, 2019

Product Classification

Regional Availability	Latin America North America
Portfolio	NETCONNECT®
Product Type	Fiber trunk cable assembly
Product Brand	MPOptimate®
Product Series	MPA

General Specifications

Color, boot A	Black
Color, boot B	Black
Color, connector A	Aqua
Color, connector B	Beige
Connector A, quantity	4
Connector B, quantity	4
Interface, Connector A	MPO-12/UPC Female
Interface Feature, connector A	Unpinned
Interface, Connector B	MPO-12/UPC Female
Interface Feature, connector B	Unpinned
Jacket Color	Aqua
Total Fibers, quantity	48

Dimensions

MPA-NCNC440034F-SS

Cord Length 10.36 m | 33.99 ft

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance