Part Number : 2064620500
Product Description : Micro-Fit+ Terminal Position Assurance (TPA) Retainer, 5 Circuits, 3.00mm Pitch, UL 94V-0, Glow-Wire Capable, Natural
Series Number : 206462
Status : Active
Product Category : Connector Accessories



Documents and Resources

Drawings

2064620500_sd.pdf

2064620000-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2064600001-AS-000.pdf

2064600000-PS-000.pdf

2159530000-PS-000.pdf

2064600000-TS-000.pdf

2064600001-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	206462
Description	Micro-Fit+ Terminal Position Assurance (TPA) Retainer, 5 Circuits, 3.00mm Pitch, UL 94V-0, Glow-Wire Capable, Natural
Component Type	Terminal Position Assurance (TPA)
Product Name	Micro-Fit+
UPC	191130008704

Agency

UL	E29179

Physical

Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Natural
Flammability	94V-0
Lock to Mating Part	Yes

Downloaded from Arrow.com.

Material - Resin	Nylon
Net Weight	0.148/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-Fit+ Dual Row Receptacle Housings	206461
Micro-Fit+ Dual Row Plug Housings	215922

Downloaded from Arrow.com.