



Part Number : [732161982](#)
Product Description : TNC Plug, Straight, Crimp,
RG-141, RG-303 and RG-58 Cable IP68, Brass Body,
Gold (Au), IP68, One Piece Per Bag, 50 Ohms
Series Number : 73216
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[732161982_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73216
Description	TNC Plug, Straight, Crimp, RG-141, RG-303 and RG-58 Cable IP68, Brass Body, Gold (Au), IP68, One Piece Per Bag, 50 Ohms
Application	RF
Comments	IP68
Product Name	TNC
Style	Cable
Type	Miniature
UPC	884982965652

Electrical

Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	12.884/g
Orientation	Straight
Packaging Type	Individual Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A

Reverse Polar	No
Wire/Cable Type	RG-58, RG-141, RG-303, LMR-195

This document was generated on Sep 13, 2025