
Part Number : 03061031
Product Description : 1.57mm Diameter Standard .062" Pin and Socket Receptacle Housing, 3 Circuits, with Standard Mounting Ears
Series Number : 1625
Status : New Business Not Supported
Product Category : Connector Housings
Engineering Number : 1625-3R



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Part Details

General

Status	New Business Not Supported
Category	Connector Housings
Series	1625
Description	1.57mm Diameter Standard .062" Pin and Socket Receptacle Housing, 3 Circuits, with Standard Mounting Ears
Application	Power, Wire-to-Wire
Comments	Polarized to Mating Part
Product Family	Standard .062"+ and Standard .062" Pin and Socket Connector Systems
Product Name	Standard .062"
UPC	800753615502

Agency

CSA	LR19980
UL	E29179

Physical

Breakaway	No
Circuits Detail	1x3
Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.069/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	Yes

Downloaded from Arrow.com.

Pitch - Mating Interface	3.68mm
Pitch - Termination Interface	3.68mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A

This document was generated on Oct 02, 2024

Downloaded from Arrow.com.