




REV.	DATE	DESCRIPTION
NC	12/09/00	INITIAL RELEASE
A	11/30/06	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex						
7						DRAWN	G.R.S.					11/30/06		
6	HEX NUT	BRASS	NICKEL	1		CHECKED								
5	LOCK WASHER	BRASS	NICKEL	1		ISSUED			PART DESCRIPTION N JACK TO BNC BULKHEAD					
4	GASKET	SILICONE	RED	1		SHEET	1 OF 1							
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	DO NOT SCALE DRAWING	PART NO. 242162								
2	INSULATOR	TEFLON	NATURAL	1		DWG. NO. 242162.DWG								
1	BODY	BRASS	NICKEL	1		REV. A SIZE A SCALE NA								
DESCRIPTION					MATERIAL	FINISH	QTY	C:/242/242162.DWG						