

## Keyspan Mini DisplayPort to Active VGA Adapter, Video Converter (M/F), White, 6-in.

MODEL NUMBER: **P137-06N-VGA**



Connect a VGA monitor to a Mac or PC with a Mini Displayport output

### Description

Tripp Lite's P137-06N-VGA Mini-DisplayPort to VGA Adapter allows you to connect a Mac or PC with a Mini-DisplayPort or Thunderbolt™ output to a VGA monitor.

Ideal for Thunderbolt™ /Mini DisplayPort equipped laptops, Chromebooks, MacBooks, Ultrabooks, and Microsoft Surface. Mac 10.11, Windows 10 Compatible.

Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Fully-molded ends ensure long life enjoyment. It features a simple plug and play design with an integrated chip that converts the digital Mini-DisplayPort signal to analog VGA; no drivers or setup needed. Simply plug the adapter into your Mini-DisplayPort source and connect your VGA cable between it and your monitor.

Unlike passive adapters, Active adapters convert both Single-Mode and Dual Mode (DP++) DisplayPort output. It is ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals.

### Features

- Connect a VGA monitor to a Mac or PC with a Mini Displayport output
- Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals

### Highlights

- Connect a VGA monitor to a Mac or PC with a Mini Displayport output
- Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

### System Requirements

- Mac or PC with a Mini Displayport port; Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Monitor with a VGA port
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P137-06N-VGA-V2

### Package Includes

- Mini-DisplayPort to Active VGA Adapter

- Converts both Single-Mode and Dual Mode (DP++) Displayport output

## Specifications

OVERVIEW	
UPC Code	037332158901
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.24
PHYSICAL	
Color	White
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 0.03
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.01
Shipping Weight (kg)	0.02
Shipping Weight (lbs.)	0.05
ENVIRONMENTAL	
Operating Temperature Range	0 C ~ 70 C
Storage Temperature Range	10 C ~ 80 C
Operating Humidity Range	10% ~ 85% RH
Storage Humidity Range	5% ~ 90% RH
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	VGA/SVGA; DisplayPort
STANDARDS & COMPLIANCE	
Certifications	RoHS
WARRANTY	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	3-year limited warranty
-------------------------------------	-------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>