
HellermannTyton

Technical data sheet

Article number:
111-02810 T18S



Product Group	Cable ties polyamide 6.6 standard
Product Family	T-Series in PA66 black
Material	Polyamide 6.6 (PA66)
Colour	Black (BK)

Application Tool	EVOcut, MK7P, MK10-SB, MK20, EVO7i, EVO7iSP
Bundle Ø max.	16.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Halogen-free	Yes
Height (H)	3.2 mm
Length (L)	83.0 mm
Min.Tensile Strength	80 N
Operating Temperature	-40 °C to +85 °C
Package Content	100 pcs.
Package Content packed in	pack
Releasable Closure (Yes/No)	No
Specifications	ANSI/UL 62275, CSA -C22.2 no. 62275
Thickness (T)	0.95 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E85319
UV-Stabilised	No
Variant	Inside Serrated
Width (W)	2.3 mm

HF RoHS

created on 18. September 2026, 6:15 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.