Part Number : 1300240191
Product Description : Mini-Change A-Size Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 22 AWG. DeviceNet Thin (Drop) Cable, 1.0m (3.28') Length
Series Number : 130024
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : DND01A-M010



Documents and Resources

Drawings

1300240191_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130024
Description	Mini-Change A-Size Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 22 AWG. DeviceNet Thin (Drop) Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	DeviceNet Trunk,Mini-Change
Type	Single Ended
UPC	78678801043

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	300V AC/DC

Physical

Cable Diameter	8.38mm (.330")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC

Downloaded from Arrow.com.

Material - Connector Body	PVC
Material - Contact	Brass
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Net Weight	111.583/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Thin (Drop)
Wire Size (AWG)	22

Downloaded from Arrow.com.