



HONEYWELL PART NUMBER	REV	DOCUMENT	CHANGED BY	CHECK
BFLI-AWI-S	A	0018413	NM 18JAN06	RJ



NOTES
1 - 3X 6-32 UNC PRESSURE PLATE TERMINAL SCREWS
2 FURNISHED UNASSEMBLED

CHARACTERISTICS	CONTACT ARRANGEMENT
OPERATING POSITION:..... 15° MAX OPERATING FORCE:..... 7 OZ MAX	S P D T L162 5A 125, 250, 277 VAC 1/10 HP 250 VAC UL E

DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:	DRAWN NM 16JAN06 CHECK RJ 16JAN06	Honeywell		
NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES X ±	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.	TITLE SWITCH, ENCLOSED		
THIRD ANGLE PROJECTION	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY	SIZE C	TYPE I	DRAWING NAME BFLI-AWI-S
	Pro/ENGINEER 3D	SCALE 1:1	SHEET 1 OF 1	