HellermannTyton

Technical data sheet

Article number:
161-64405 **HWPP25L2**



Product Group	Helawrap cable cover
Product Family	HWPP in polypropylene
Material	Polypropylene (PP)
Colour	Grey (GY)

Bundle Ø max.	27 mm
Bundle Ø min.	23 mm
Flammability	UL 94 HB
Nominal Ø	25 mm
Operating Temperature	-60 °C to +110 °C, intermittent +140 °C
Package Content	2 m
Package Content packed in	pack
Specifications	ECE R-118-03 Abschnitt 6 / Annex 6
Wall (WT)	1.05 mm

HF RoHS

ECE R-118

created on 31. July 2026, 4:02 am

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.