




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP	11JUN2023	ED	WH

NOTES:

1. ALL RF CONNECTORS MUST BE ASSEMBLED PER MANUFACTURER’S APPLICATION SPECIFICATIONS WITH FOLLOWING [SC]:
1.1: SOCKET CONTACTS CRIMP HEIGHT
1.2: FERRULES’ CRIMP HEIGHT
1.3: CONNECTORS TO COAX CABLE RETENTION FORCE
2. 100% IN-PROCESS ELECTRICAL TEST:
2.1: DC CONTINUITY, FOR CENTER AND OUTER CONDUCTORS, POINT TO POINT
2.2: SHORT CIRCUITS;
3. TEMPERATURE RANGE: -40°C TO 85°C
4. MAX FREQUENCY IS 3GHz

5. LABEL CONTENT:

TE P/N: XXXXXX-X REV: X

DATE: YYYYMMDD

X: FOLLOW DRAWING REVISION

X: -1 OR -2 OR-3

DESCRIPTION:
YYYY: YEAR (EXAMPLE: 2016) MM:
MONTH (EXAMPLE: 02)
DD: DATE (EXAMPLE: 25)

TE P/N	LENGTH L(mm)
2081345-1	300 ⁺¹⁰ ₀
2081345-2	600 ⁺¹⁰ ₀
2081345-3	1000 ⁺¹⁵ ₀
2081345-4	2000 ⁺²⁰ ₀
2081345-5	3000 ⁺³⁰ ₀
2081345-6	5000 ⁺⁵⁰ ₀

			1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	LABEL	4
			5m	3m	2m	1m	0.6m	0.3m	COAXIAL CABLE RG58LL	3
			1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	SMA PLUG, RG58 CABLE	2
			1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	1 PCS	FAKRA JACK CODE Z WATER BLUE, RG58 CABLE	1
			2081345-6	2081345-5	2081345-4	2081345-3	2081345-2	2081345-1	DESCRIPTION	ITEM

QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
-

DWN
ED
24MAR2023

CHK
RZ
24MAR2023

APVD
WH
24MAR2023

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

CABLE ASSEMBLY, RG58LL CABLE,
FAKRA FEMALE CODE Z TO SMA MALE.
LENGTH IS L

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2081345

RESTRICTED TO
-

SCALE
-

SHEET
1 OF 1

REV
A