




Part Number : [936000065](#)
Product Description : Heavy-Duty Metal Gable
Gland - 5 Bar, for 30.00-38.00mm Cable, Pg42 Thread
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Number : 7000.6897.0



Documents & Resources

Drawings

[936000065 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Gable Gland - 5 Bar, for 30.00-38.00mm Cable, Pg42 Thread
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Product Name	Heavy-Duty Connectors
UPC	887191829876

Physical

Cable Diameter	30.00-38.00mm
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	313.000/g
Packaging Type	Bag
Panel Cutout Diameter	54.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg42
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Mates With / Use With

Use with Part(s)

Description	Part Number
-------------	-------------

Use With	Industrial connector hoods and housings
----------	---

This document was generated on Sep 25, 2025