

Search within category

GO

PPMA1477B

PROCESS WATER

Pipe marker, 'PROCESS WATER' (legend), Yellow, Size B. Dura-Polyester Vinyl.
Sold in US and Canada only

BUY NOW

DESIGN / INSTALL

Specs		Packaging Details	Documents	★ Add to Favorites		🛒 Add to BOM
Material		Dura-Polyester Vinyl				
Overall Width (mm)		203.2				
Overall Height (mm)		38.1				
Note		Sold in US and Canada only				
Application		Mark and identify contents in pipes and piping systems, including flow directions and hazard classification for maintenance and safety purposes. Pipe markers are designed in accordance to ASME (ANSI) A13.1 recommendations for sizes, colors, and visibility.				
Color		Black/Yellow				
Diameter (mm)		50.8				
Dimensions (In.)		1.5" x 8"				
Environment		5-7 years				
Legend		PROCESS WATER				
Maximum Operating Temperature (°C)		80				
Maximum Operating Temperature (°F)		176				
Maximum Overall Height (mm)		38.1				
Minimum Operating Temperature (°C)		-28				
Minimum Operating Temperature (°F)		-20				
Part Features		6-mil thick poly-composite vinyl with permanent acrylic adhesive backing scored liner for quick peel-off to apply onto pipe., Sub-surface image is protected by a high-gloss UV protective coating and is resistant to abrasions, humidity, chemicals, solvents, and fading from sunlight, Includes detachable arrow to provide proper directional flow marking, Fits pipe diameter 1.5" to 2"				
Thickness (mm)		0.1016				
UL Listed		No				
RoHS Compliancy Status		Compliant				
Min. Order Qty.		1				
Sub Brand		Stock Pipe Markers				