



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	SIGNAL				
		E2	4	3	2	1
51940-136-- NOTE 3	D C B A		F	F	F	F
			F	F	F	F
			F	F	F	F
			F	F	F	F



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
F	N/A [N/A]	SIGNAL

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		
								COPY		www.fciconnect.com		
lir	ecr no.	dr	date	linear	.XX±.01/0.X±0.3		projection		title	16S		
A	DG05-0073	SLUO	4/5/05		.XXX±.005/0.XX±0.13					VERTICAL PF RECEPT		
B	DG06-0181	RYAN	05/10/06		.XXX±.0020/0.XXX±0.051							
				angles	0°±2°		INCH/MM		product family	PwrBlade		
				dr	SLUO	4/5/05				code	213	
				enrg	SLUO	4/5/05						sheet
				chr	VICTOR LIN	4/5/05						
				appd	JOSEPH HSIA	4/5/05	scale	1:1	A			51940-136
sheet index		revision		B	B	A						
		sheet		1	2	3	4					

cage code 22526

Pro/E

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.


coge code	22526
-----------	-------

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51940-136--
NOTE 3



mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		FCI	
lir	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	COPY		www.fciconnect.com	
B					.XXX±.005/0.XX±0.13	projection		title 16S	
				angles	.XXX±.0020/0.XXX±0.051			VERTICAL PF RECEPT	
				dr	SLUO 4/5/05	INCH/MM		product family PwrBlade	
				enrg	SLUO 4/5/05	scale		size 213	
				chr	VICTOR LIN 4/5/05	1:1		dwg no 51940-136	
				appd	JOSEPH HSIA 4/5/05			sheet 3 of 4	
sheet index	revision	sheet							

Pro/E

cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51940-136--
NOTE 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

- 2 HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
SIGNAL PIN MATERIAL: COPPER ALLOY
3. PLATING:
SEE PRINT 10064183 FOR PLATING SPEC OF 51940-136; 51940-136LF
- 4 NO LASER MARK ON THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
6. PACKAGED IN TRAYS.
- PCB NOTES:
7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
8. $\varnothing .0453 \pm .0010$ [1.151 $\pm$ 0.025] DRILLED HOLES PLATED WITH
.0003 [0.008] MIN SnPb OVER .001 [0.03]
TO .003 [0.08] Cu PLATING TO ACHIEVE
 $\varnothing .040 \pm .003$ [1.02 $\pm$.07] HOLE.
9. "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
10. CONNECTOR KEEP-OUT ZONE.

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
lfr	ecn no.	dr	date	linear	.XX $\pm$.01/0.X $\pm$ 0.3	COPY		www.fciconnect.com	
B				linear	.XXX $\pm$.005/0.XX $\pm$ 0.13	projection		title	16S
				angles	.XXX $\pm$.0020/0.XXX $\pm$ 0.051			VERTICAL PF RECEPT	
				dr	SLUO 4/5/05	INCH/MM		product family	PwrBlade
				engr	SLUO 4/5/05	scale		size	213
				chr	VICTOR LIN 4/5/05	1:1		dwg no	51940-136
				appd	JOSEPH HSIA 4/5/05			sheet	4 of 4
sheet index	revision sheet								

Pro/E

cage code 22526