




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/21/11	
A		REVISED DIM.	6/13/16	AY/LL



SPECIFICATIONS:

Material:
 Insulator: Hi-temp thermoplastic, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass
 Shell: Brass, Matte Tin plated.
 Plating:
 Gold over Nickel underplate on contact area
 Electrical:
 Operating voltage: 30 VAC/DC.
 Current rating: (P1 & P5): 1.8A, (P2, P3, P4): 0.5A.
 Contact resistance: 30 mohms max.
 Insulation resistance: 1000 Mohms min.
 Dielectric withstanding voltage: 100 VAC for 1 minute
 Temperature Rating:
 Operating temperature: -30°C to +80°C
 Packaging:
 Supplied on Tape & Reel
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ±.10 Ø.X ±.10 .XX ±.020 Ø.XX ±.015 .XXX ±.015 Ø.XXX ±.010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS DRAWN CHECKED APPROVED			DATE 4/21/11		
TITLE MICRO USB, TYPE B, SINGLE PORT FEMALE, DIP SHELL, SMT TYPE, TAPE & REEL			SIZE X		
PART NO. MCR-B-S-RA-SMT-CS1-T/R			REV. A		
REF: S00005C			SCALE: NTS		
SHEET 1 OF 1			SHEET 1 OF 1		