



Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

General

Provided equipment	Installation guide
--------------------	--------------------

Physical

Colour	Black
Depth	670.6 cm
Height	6.4 cm
Net weight	3.18 kg
Width	5.1 cm

Input

Plug standard	NEMA L21-20P
Permissible voltage	200...240 V
Max line current	20 A
Input voltage	208 V 3 phases

Output

Max current draw	20 A
Output voltage	120 V 208 V 3 phases

Conformance

Product certifications	UL listed
------------------------	-----------

Packing Units

Package 1 Weight	3.5 kg
Package 1 Height	10.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 width	30.5 cm
Package 1 Length	44.5 cm

### Offer Sustainability

EU RoHS Directive	Not compliant
-------------------	---------------

### Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------