




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2025-03-03	Henry	Rev.01 To Rev.A
B	C250706	2025-05-28	Henry	△B X2












Recommended installation orientation

建議安裝朝向



Recommended Panel Cut-Out

建議開孔尺寸

Note:
* QC Important Dimension.
* Waterproof Rate: IP68(2m/1h)
△B * Body: PC, Gray.
* Membrane: ePTFE
* O-Ring: Rubber, Black.
* Air Permeability: >16L/min @1.2 kPa
* Temperature Resistance: -40~125℃
* Recommended installing torque: 5N.m
* Recommended plate thickness: T > 4.0mm.
* All Parts Are RoHS Compliant.

UNIT: mm

TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE: BREATHABLE VENT, PLASTIC, M32

SCALE 2:3 | SIZE A4 | SHEET 1 OF 1

REV. B | WC-REV. .0 | QC: Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
VT-BPM32GY-NO8001	Henry	2025-05-28
DWG NO: VT-BPM32GY-NO8001	CHECKED BY: Jerry	DATE: 2025-05-28
CUSTOMER: ALTW	APPROVED BY: Fred	DATE: 2025-05-28

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Downloaded from Arrow.com.