

Part Number : [191290020](#)


Product Description : Krimptite Block Spade Terminal for 16-14 AWG Wire, Carton

Series Number : 19129

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : BB-1781-10



Documents and Resources

Drawings

[191290020_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19129
Description	Krimptite Block Spade Terminal for 16-14 AWG Wire, Carton
Keyword	Spade Terminal, Spade Terminals
Product Name	Krimptite
Style	Spade Block
Type	Spade Connector, Metric Spade Connector
UPC	800755083828

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.617/g
Packaging Type	Carton
Plating min - Mating	2.540µm

Plating min - Termination	2.540µm
Stud Size	10 (M5)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm ²	1.30-2.00

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

This document was generated on May 21, 2026