




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	REVISED PER ECN-23-240868	24NOV2023	AP	IT

1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3. MATERIAL: HOUSING AND COVER - POLYPHENYLENE OXIDE.
CABLE CLAMP - POLYESTER MOLDING COMPOUND.
TERMINAL - HIGH STRENGTH COPPER ALLOY PLATED WITH 0.76µm [.000030] MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, 0.76µm [.000030] MIN TOTAL ON MATING SURFACE, OVER 1.27µm [.000050] MIN NICKEL UNDERPLATE.
HARDWARE - ZINC PLATED STEEL.
DUST COVER - POLYETHYLENE MOLDING COMPOUND.
4. THIS KIT SHIPPED NOT ASSEMBLED.
5. WIRE SIZE: 24 & 26 AWG SOLID & 24/7 STRAND COPPER CONDUCTORS. MAXIMUM INSULATION DIAMETER OF 1.14 [.045] IS ACCEPTABLE FOR MOST APPLICATIONS.
6. CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF AMP INCORPORATED.
7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

BULK PACKED	ø7.62-8.26 [ø.300-.325]	YES	BLACK	6-5229912-7
	ø8.89-10.80 [ø.350-.425]	YES	GRAY	6-5229912-4
		YES	BLACK	6-5229912-3
POLY BAGGED	ø10.80-12.70 [ø.425-.500]	NO	BLACK	6-5229912-1
		YES	BLACK	3-5229912-1
	ø8.89-10.80 [ø.350-.425]	NO	BLACK	2-5229912-1
OBSOLETE		YES	BLACK	1-5229912-1
		NO	GRAY	5229912-4
		NO	BLACK	5229912-1
PACKAGING	CABLE RANGE	DUST COVER	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN G.PETERS 23SEP2005	TE Connectivity			
				CHK W.MILLHIMES 23SEP05				
				APVD M.WALMSLEY 23SEP05	NAME			
				PRODUCT SPEC	PLUG KIT, 50 POSITION, B-SLOT SCREW LOCK WITH TAPERED COVER, CHAMP-LOK			
				APPLICATION SPEC				
					SIZE A2	CAGE CODE 00779	DRAWING NO C=5229912	RESTRICTED TO -
				WEIGHT 0.000000				
				CUSTOMER DRAWING				