



Part Number : [1301020091](#)

Product Description : Super-Safeway Rubber Hand Lamp with 100W, Quick Open Guard with Reflector, with Switch and Side Outlet, Cord Length 7.62m (25.0'), Cord Type 16/3 SOOW

Series Number : 130102

Status : Active

Product Category : Lamps and Lights

Engineering Number : 105USA163



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130102
Description	Super-Safeway Rubber Hand Lamp with 100W, Quick Open Guard with Reflector, with Switch and Side Outlet, Cord Length 7.62m (25.0'), Cord Type 16/3 SOOW
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678879410

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	Yes
Guard Type	Quick Open, Reflector
Height	374.65mm (14.750")
Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	Side

Packaging Type	Carton
----------------	--------

This document was generated on Sep 18, 2025