






| REV. | DATE     | ECR NO. | DESCRIPTION                           |
|------|----------|---------|---------------------------------------|
| NC   | 04/22/07 | —       | INITIAL RELEASE                       |
| A    | 10/15/08 | —       | REVISE 174/U TO 179/U CABLE CALL OUT. |



RECOMMENDED  
CABLE STRIPPING DIM'S



NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .178" [4.52]
2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068" [1.73]

|   |             |          |         |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |                               |          |                                                                              |                          |      |   |       |    |
|---|-------------|----------|---------|-----|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|-------------------------------|----------|------------------------------------------------------------------------------|--------------------------|------|---|-------|----|
|   |             |          |         |     | <div>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.</div> <div>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:<br/>0.5 – 8mm ± 0.20mm<br/>8 – 30mm ± 0.40mm<br/>30 – 120mm ± 0.50mm</div> <div>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:<br/>.020 – .315 = ± 0.007”<br/>.315 – 1.180 = ± 0.015”<br/>1.180 – 4.724 = ± 0.020”</div> <div>DO NOT SCALE DRAWING</div> | APPROVALS |                               | DATE     |                                                                              | <h1>Amphenol Connex</h1> |      |   |       |    |
| 8 |             |          |         |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | DRAWN     | G.R.S.                        | 10/15/08 |                                                                              |                          |      |   |       |    |
| 7 |             |          |         |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | CHECKED   |                               |          | PART DESCRIPTION<br><br>TNC CRIMP PLUG<br>(FOR RG-179/U, 187/U, B9221 CABLE) |                          |      |   |       |    |
| 6 |             |          |         |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | ISSUED    |                               |          |                                                                              |                          |      |   |       |    |
| 5 | FERRULE     | COPPER   | NICKEL  | 1   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | SHEET     | 1 OF 1                        |          | PART NO.<br><br>122117                                                       |                          |      |   |       |    |
| 4 | SLEEVE      | DELIRIN  | NATURAL | 1   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |                               |          |                                                                              |                          |      |   |       |    |
| 3 | INSULATOR   | DELIRIN  | NATURAL | 1   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |                               |          |                                                                              | DWG. NO. 122117.DWG      |      |   |       |    |
| 2 | CONTACT PIN | BRASS    | GOLD    | 1   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |                               |          |                                                                              |                          |      |   |       |    |
| 1 | SHELL/BODY  | BRASS    | NICKEL  | 1   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |                               |          | REV.                                                                         | A                        | SIZE | A | SCALE | NA |
|   | DESCRIPTION | MATERIAL | FINISH  | QTY |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           | CAD FILE<br>C:/122/122117.DWG |          |                                                                              |                          |      |   |       |    |