



**Part Number :** [1300000090](#)

**Product Description :** Quick-Change Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 12 AWG, Yellow CPE Cable, 3.66m (12.0') Length

**Series Number :** 130000

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 32679



---

## Documents and Resources


### Drawings

[1300000090 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025) SCIP:a5173ccd-2892-4522-81b2-fd128d3180b0
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	130000
Description	Quick-Change Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 12 AWG, Yellow CPE Cable, 3.66m (12.0') Length
IP Rating	IP67
Product Name	Quick-Change
Type	Single Ended
UPC	78678832679

### Agency

CSA	LR6837
UL	E46237

### Electrical

Current - Maximum per Contact	20.0A
Voltage - Maximum	600V

### Physical

Cable Diameter	18.03mm (.710")
Cable Length	3.66m (12.0')
Color - Cable Jacket	Yellow

Connector End A	Quick-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	CPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nylon
Material - Plating Mating	N/A
Net Weight	1623.861/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	SOW
Wire Size (AWG)	12

---

This document was generated on Dec 16, 2025