3D CAD | Product Specification | PDF Catalog

Part number AFR14A901B **AFR14 Series**

Automotive

Standard | Print

MEMBERS ONLY Save Item | Contact

Basic information | Dimensions | Packing Specifications

Basic information

+ ZOOM

Resonance frequency	120Hz
Size	23.0×33.0×13.0mm
Vibration Acceleration	15Gpp
Drive voltage	6Vp-p (20 sine wave)
Operating temperature	-40°C to +85°C

Specifications

Resistance		10.2Ω±10% (@20°C)
Minimum order unit(pcs.)	**Japan**	200
	Export	200

Dimensions



Open an expandable image in a separate window

Packing Specifications

Tray

Number of packages (pcs.)	
1 case / Japan	200
1 case / export packing	200

Export package measurements (mm)
270×360×185

Notes are common to this series/models

1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
2. Please place purchase orders per minimum order unit (integer).

Inquiries about Products

Category List

Sensors

Semiconductors

TACT Switch™

Switches

Encoders

Potentiometers

Connectors →

Wireless Communication Devices

Multi Control Devices

Aspherical Glass Lenses

Actuators →

haptic reactor →

Capacitive Sensing Modules →

© 2026 ALPS ALPINE CO., LTD.

Downloaded from Arrow.com.