

ENCLOSURE HARDWARE

LED INDICATORS

LIGHT PIPE SELECTOR

LED MOUNTS, HOLDERS

LEDs

LIGHT PIPES

BOARD MOUNT LED ASSEMBLIES

PANEL MOUNT LED ASSEMBLIES

LED LIGHTING

SOLUTIONS

RESOURCES

FLPR4.5-SUR



Flexible Light Pipe Assembly, 1mm. Fiber Optic Core, Right Angle, 4.2mm. Dia. Low Profile Lens, 4.5in. Length, 3mm LED, Super Ultra Red



Datasheet



3D Model



Request Samples



RoHS Docs

FEATURES	VALUE ADDED	CHECK STOCK
<ul style="list-style-type: none">Wavelength: 640nm, Typical Intensity: 200mcd, Color: RedAssembly Includes Flexible Light Pipe, Right Angle Through-Hole Adaptor and LED4.2mm. Diameter Low Profile Lens CapFlexible Light Pipe Cable Customized Length-See Specification Sheet for More InfoMaterial: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 ClearFront Panel Mount Lens		



Enclosure Hardware
LED Indicators
LED Lighting

New Products
Locate a Distributor / Sales REP
Quality Assurance / RoHS

Product Info Center
Terms & Conditions
My Bivar



100% Employee Owned