



Catalog No. 54512A

Description: 54512 MADE TO ABB DIMENSIONS

UPC No 786209913838

Home > Connectivity & Grounding > Color Keyed / Blackburn > Wire or cable compression splice

Copper Two-Way Splice Connector, Standard Barrel, Peep Hole, Max 35kV, Wire Size 4/0 AWG, Plain Finish, Die Code 54, Die Color Code Purple, Length 1.48 Inches

Descriptors	
Category	Wire or cable compression splice

Specifications	
Material	Copper
Finish	Plain (No) Finish
Color	Purple
Voltage Rating	35 kV
Insulation	None

Classifications	
Brand Name	Color Keyed / Blackburn

ETIM	EC001059 Crimp splices for copper conductor
AWG-range	4/0-4/0
Sleeve form	Short
Material	Copper
Surface protection	Bare
Insulation	None
Voltage level	Up to 35 kV
Type of connection	End connector