







SECTION A-A'




- NOTE -

1. TOLERANCE IN: ± 0.1 UNLESS OTHER SPECIFIED.
2. CO-PLANARITY: 0.1 max.
3. PART NUMBER: 10102783-001LF



Reference PCB Pattern
(General Tolerance : ± 0.05)



Co-planarity Measurement

No.	Part Name	Material	Finish
1	Housing	Thermoplastic	Black
2	Contact Terminal	Copper Alloy	Ni: 1.27-3.0 um Au: Selective 0.2um on contact Au: 0.03um on tail
3	Shield	Stainless Steel	Ni: 1.27-3.0 um

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	angles	projection	title	www.fciconnect.com	
A	T10-0040	J H	4/26/10	.X ± 0.20	0' $\pm 2'$	MM	MMI 20P RECEPTACLE		
B	T10-0066	J H	5/21/10	.XX ± 0.10		scale	product family 582	code TWN	
				.XXX $\pm$		3:1	size dwg no	sheet 1 OF 1	
				dr JASON HSU	4/26/10		10102783		
				enr JASON HSU	4/26/10				
				chr GARY HSIEH	4/26/10				
				appd JOSEPH HSIA	4/26/10				
sheet index	revision	B							
	sheet	1							