

Home >

Downloads:

Series: Micro-Con-X [refresh](#)

Connector Type:

Coupling Style:

Contact Number:
contact arrangement

Contact Size: [i](#) only one option available

Contact Style:

Contact Gender:

Contact Plating: [i](#) only one option available

Rear Style:

Insert Material: [i](#) only one option available

Color Option: [i](#) only one option available

Wing Option: [i](#) only one option available

Part Number: **W17882-4PG-P-300**

UV resistant thermoplastic insert panel mount connector #22 solder cup 4-position pin (male) gold over nickel plating Insta-Click™ hex nut and gasket (no epoxy) no color option (standard black); No Wing (Standard)



 3D CAD model available (STEP format) - Registered Users Only

DXF and STEP files are available only to registered users. If you are already a registered user [login here](#) . If you have not yet registered [sign up here](#).

Notes: PC Tail sizes .280 and .335 are only available in #20 contacts.
Insta-Click™ connectors are only available in black UV resistant material
Winged coupling nuts are only available on cable-end connectors
Consult factory for optional threaded coupling
Consult factory for custom designed cable assemblies and connectors.