

# Product data sheet

Specifications



## APC NetShelter Cable Management, Cable Ladder Attachment Kit, for 2 Post Rack, Black

AR8460

### Overview

|              |  |
|--------------|--|
| Presentation | Allows cable ladders to attach to 2-post racks, running parallel and perpendicular to a row of racks. This increases agility by providing solutions for environments with layout challenges. |
| Lead time    | Usually in Stock   |

### Main

|                    |                    |
|--------------------|--------------------|
| Provided equipment | Installation guide |
|--------------------|--------------------|

### Physical

|                            |                    |
|----------------------------|--------------------|
| Colour                     | Black              |
| Height                     | 10.2 cm            |
| Width                      | 35.6 cm            |
| Depth                      | 7.6 cm             |
| Net weight                 | 1.18 kg            |
| Mounting preference        | No preference      |
| Mounting mode              | Not rack-mountable |
| Permanent permissible load | 52.16 kg static    |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | Db      |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 12.7 cm |
| Package 1 Width              | 8.3 cm  |
| Package 1 Length             | 38.1 cm |
| Package 1 Weight             | 1.64 kg |

### Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Green Premium product   |
| REACH Regulation         | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC       | Yes   |
| EU RoHS Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |

|                            |                             |
|----------------------------|-----------------------------|
| Toxic heavy metal free     | Yes                         |
| Mercury free               | Yes                         |
| RoHS exemption information | Yes                         |
| Take-back                  | Take-back program available |

Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

Recommended replacement(s)