











PCB layout, component side



Max. Temperature: 260°C during 10 seconds.
Find further technical information on DS 09550200302

0955 229 6812 333	2	4-40 UNC	Black insulator	Samples
0955 229 3811 741	1	M3	Black insulator	Reel packing: 140 connectors
0955 229 3812 741	1	4-40 UNC		
0955 229 6811 741	2	M3		
0955 229 6812 741	2	4-40 UNC		
0955 229 7811 741	3	M3		
0955 229 7812 741	3	4-40 UNC		
Part number	PL	Nut	Index designation	

		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved		Created by ZHUANGJ		Inspected by LUOK		Standardisation HOFFMANN		Date 2018-11-29		State Final Release			
Department EL PD				Title D-Sub str SMT 15-pole male with screw nut & ground pad								Doc-Key / ECM-Nr. 100236645/UGD/001/C 500000139800			
HARTING Electronics GmbH				Type TB		Number 0955229X81X						Rev. C		Page 1/1	
D-32339 Espelkamp															