



## GD1926, Mech Ground, 2 Cables to Rod or Pipe

By Burndy

Catalog # [GD1926](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 2-1/2" Rod, 2-1/2" Pipe.



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

Specifications

|                                         |       |
|-----------------------------------------|-------|
| Certification - UL Recognized           | No    |
| Buy American Compliant                  | No    |
| Certification - cULus                   | No    |
| EU RoHS Indicator                       | Yes   |
| Industry Standard(s)                    | UL467 |
| Certification - ETL                     | No    |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | EX    |
| Certification - UL Listed Direct Burial | Yes   |
| UL Listed                               | Yes   |
| Certification - CSA Approved            | No    |

Conductor

|                                     |                                                                                                                     |
|-------------------------------------|---------------------------------------------------------------------------------------------------------------------|
| Conductor - Rod Size Range          | 2 1/2 in                                                                                                            |
| Conductor - Copper Str Size         | <ul style="list-style-type: none"><li>• 4</li><li>• 3</li><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li></ul> |
| Conductor - Rod Size                | 2 1/2 in                                                                                                            |
| Conductor - Copper Solid Size       | <ul style="list-style-type: none"><li>• 4</li><li>• 3</li><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li></ul> |
| Conductor - Copper Solid Size Range | 4-2/0                                                                                                               |
| Conductor - Copper Str Size Range   | 4 AWG - 2/0 AWG                                                                                                     |

|                                        |       |
|----------------------------------------|-------|
| Conductor - Copper Str Size B Range    | 2.5   |
| Conductor - Copper Tube Std Size Range | 2-1/2 |
| Conductor - Copper Tube Std Size       | 2-1/2 |

Dimensions

|                             |           |
|-----------------------------|-----------|
| Package Height              | 0.000 in  |
| Dimension - Height mm       | 127 mm    |
| Dimension - Height inch     | 5.00 in   |
| Dimension - Height fraction | 5 in      |
| Package Weight              | 0.000 lb. |
| Package Length              | 0.000 in  |
| Package Width               | 0.000 in  |
| Dimension - Width fraction  | 4-1/4 in  |
| Dimension - Width mm        | 106 mm    |
| Dimension - Width inch      | 4.19 in   |
| Dimension - B Length inch   | 1.38 in   |

Force Related

|                     |            |
|---------------------|------------|
| Installation Torque | 240 LBS/in |
| Recommended in-lb   |            |

General

|                              |                          |
|------------------------------|--------------------------|
| Material Type - Screw Plated | DURIUM™ Silicon Bronze N |
| Sub Brand                    | MECHANICAL CONNECTOR     |
| UPC                          | 781810260364             |
| Type                         | GD                       |
| U Bolt Type                  | 266                      |
| Material                     | Copper Alloy, Cast       |
| Plating Type                 | Unplated                 |
| UPC 12 Digit                 | 781810260364             |
| UPC 14 Digit GTIN            | 00781810260364           |

Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 1200 |
| Carton Quantity       | 12   |

Product Assets

[Catalog \[English\]](#)



A Hubbell brand