Part Number : 190350009
Product Description : Avikrimp Snap Plug, for 16-14 AWG Wire, Box, 22.55mm Length, Carton
Series Number : 19035
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : B-589



Documents and Resources

Drawings

190350009_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19035
Description	Avikrimp Snap Plug, for 16-14 AWG Wire, Box, 22.55mm Length, Carton
Comments	Molded Nylon Insulation
Product Name	Avikrimp
Type	Snap Plug
UPC	800753047921

Agency

CSA	LR18689
UL	E152602

Electrical

Voltage - Maximum	N/A

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Gender	Male

Downloaded from Arrow.com.

Glow-Wire Capable	No
Insulated	Partial
Insulation	Nylon (PA)
Lock to Mating Part	No
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.526/g
Orientation	Straight
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	N/A
Tab Width	N/A
Wire Insulation Diameter	4.32mm max.
Wire Size (AWG)	14, 16
Wire Size mm^2	1.30-2.00

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm^2 (Rings, Spades, Hooks, Block Spades and Flanged Spades)	640010100
Crimp Head for the AT-200 Pneumatic Hand Tool	640050100
ServiceGrade Hand Crimp Tool for Field Repair only, for	640160036

Downloaded from Arrow.com.

production use our PremiumGrade Tool	

Downloaded from Arrow.com.