



Part Number : [1300680079](#)

Product Description : BradPower D-Size (1 3/8"-M35) 4-Pole Trunk Tee, with 4-Pole BradPower D-Size (1 3/8"-M35) Drop, Gray



Series Number : 130068

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Number : TC40C40-200

Documents & Resources

Drawings

[1300680079_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | ⓘ per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

| | |
|--------------|--|
| Status | Active |
| Category | Industrial Tees and Splitters |
| Series | 130068 |
| Description | BradPower D-Size (1 3/8"-M35) 4-Pole Trunk Tee, with 4-Pole BradPower D-Size (1 3/8"-M35) Drop, Gray |
| IP Rating | IP67 |
| Product Name | BradPower D-Size |
| Type | Power Tap Tee |
| UPC | 78172553712 |

Agency

| | |
|----|---------|
| UL | E258922 |
|----|---------|

Electrical

| | |
|-------------------------------|------------|
| Current - Maximum per Contact | 25.0A |
| Voltage - Maximum | 600V AC/DC |

Physical

| | |
|----------------------|-------------------------------|
| Drop Connector | BradPower D-Size (1 3/8"-M35) |
| Drop Gender | Female |
| Keyway | Single |
| Left Trunk Connector | BradPower D-Size (1 3/8"-M35) |
| Left Trunk Gender | Female |
| Leg 1 Length | N/A |
| Leg 2 Length | N/A |

| | |
|-------------------------------|-------------------------------|
| Material - Cable Jacket | N/A |
| Material - Connector Body | PVC |
| Material - Coupling Nut | Anodized Aluminum |
| Net Weight | 303.907/g |
| Poles | 4 |
| Right Trunk Connector | BradPower D-Size (1 3/8"-M35) |
| Right Trunk Gender | Male |
| Temperature Range - Operating | -20°C to +90°C |

This document was generated on Sep 25, 2025