



Part Number : [1301360029](#)
Product Description : Super-Safeway Multi-Tap (3)
NEMA 5-20 Outlet Box with Buss Bars, 7.62m (25.0')
Cord Length, 14/3 SOOW Cord, NEMA 5-20 Plug
Series Number : 130136
Status : Active
Product Category : Power Distribution
Engineering Number : 31565A143



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power Distribution
Series	130136
Description	Super-Safeway Multi-Tap (3) NEMA 5-20 Outlet Box with Buss Bars, 7.62m (25.0') Cord Length, 14/3 SOOW Cord, NEMA 5-20 Plug
Enclosure Rating	N/A
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	Multi-Tap and Strip Cordset
UPC	78678875619

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	120V

Physical

Cord Diameter	13.59mm (.535")
Cord Grip Body Size	Double C-Clamp
Cord Length	7.62m (25.0')
Cord Type	14/3 SOOW
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Mounting Style	Portable

Number of Receptacles	3
Packaging Type	Carton
Receptacle Type	Triple

This document was generated on Sep 22, 2025