

PRODUCT NO.	MATERIAL
68106-XXXLF	PLAIN NORYL, COLOR: BLACK UL94V-1
68106-XXXHLF	Zytel: FR-50, BLACK UL94V-0



P/N	No.of POS	A	B	C	D
68106-003LF,-003HLF	8	5.08/.200	10.27/.404	12.27/.483	13.84/.545
68106-002LF,-002HLF	6	2.54/.100	7.73/.304	9.73/.383	11.30/.445
68106-001LF,-001HLF	4	0/.0	5.19/.204	7.19/.287	8.76/.345

NOTE

1. PUT DD MARK IN THIS PLACE
WITH 0.02/.008 HEIGHT
2. PUT CAV NO. 1.2.3.4. IN THIS PLACE
WITH 0.02/.008 HEIGHT
3. THIS PRODUCT MEETS EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.
4. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED
TO A MANUFACTURING SOLDER PROCESS.

注 記

1. この位置にDDマークを彫刻。
浮き出し高さ0.02MAX.
2. この位置にCAV No. 1.2.3.4を彫刻
浮き出し高さ0.02 MAX.
3. 本製品は、GS-22-008に記載された
ヨーロッパ指令と他国の規制に適合しています。
4. 本製品は、はんだ付け工程には使用できません。



SECT "X"-"X"

mat'l. code				surface	tolerance	projection	product family	CODE
---				ISO 1302	ISO 406	ISO 1001	5NGF - PV HOUSINGS	JP
ltr	description	ecr no	dr	date	tolerances	units	mm/INCH	title
A	RELEASED			NY 11/10/83	angles	0.X	±0.25	POLARIZED M/L HSG SHROUD DOUBLE ROW
B	REVISED	J8110	NY	12/5/84	linear	0.XX	±0.25	
C	REVISED	J8461	NY	8/5/87	0'±2'	0.XXX	±0.25	
D	ADD NEW P/N	J03-0441	YK	10/29/03	dr	D.DETOUILLOIN	27/06/18	dwg no
E	REVISED	J05-0578	R.S	9/7/05	enrg	L.MULIN	27/06/18	sheet 1 of 1 size
F	REVISED	J06-0370	R.S	10/2/06	chr	L.MULIN	27/06/18	68106
G	REVISED	F-30562	DDE	27/6/18	appd	A.SOUDY	27/06/18	A3
sheet	revision							
index	sheet	1						
		type	PRODUCT	CUSTOMER	Drawing	Rev.		
						G		