216EP4

Industrial Plug

2CMA101946R1000



Industrial Plugs, 2P+E, 16A, 100 … 130 V Clock Position Of Grounding Contact 4 hour Color code Yellow

GENERAL

Product Name	Industrial Plug
Product ID	2CMA101946R1000
Function	Plug
EAN	739269194
Catalog Description	Industrial Plugs, 2P+E, 16A, 100 … 130 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420045
E-Number Norway	
E-Number Sweden	E2416160
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EP
Color	Yellow
Number of Poles	3
Clock Position	4Hour
Rated Current	16 ampere
Rated Voltage	100 ... 130 volt
Frequency	50 hertz|60 hertz
Degree of Protection	IP44
Cable Cross-Section	1...2.5 mm²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	57 millimetre
Product Net Height	63 millimetre
Product Net Length	127 millimetre
Product Net Depth	127 millimetre
Product Net Weight	0.11 kilogram

PACKAGING

Package Width	120 millimetre
Package Height	285 millimetre
Package Gross Weight	1.1 kilogram
Package Length	138 millimetre
Package Units	box 10 piece

Downloaded from Arrow.com.