© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

CONNECTOR HOUSINGS







✔ Active

TE CONNECTIVITY (TE)

DT RECPT 12way, A key, w-flange

DEUTSCH | DT

DT04-12PA-CL06

TE Internal Number: DT04-12PA-CL06

EU RoHS Compliant
EU ELV Compliant

Connector System Wire-to-Wire

Connector Style Housing for male terminals

Sealable Yes

Mating Pin Diameter 1.5 mm [.06 in]

Circuit Application Signal

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

RECEPTACLE, 12PIN -CL06 MOD DT SERIES

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

Downloaded from Arrow.com.

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

DT Series Connector System

PDF

English

Qualification Test Report

DEUTSCH DT Series Electrical Connectors

PDF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Wire
Connector Style Housing for male terminals
Sealable Yes
Hybrid Connector No
Terminates To Wire & Cable
Primary Locking Feature Integrated in Housing
Strain Relief Add By Accessory

Configuration Features

Number of Positions 12
Number of Rows 2

Body Features

Cable Exit Angle 180°
Body Material PA GF
Color Black

Contact Features

Mating Pin Diameter 1.5 mm [.06 in]

Mechanical Attachment

Downloaded from Arrow.com.

Mounting Feature No
Terminal Position Assurance No
Polarized Yes

Operation/Application

Circuit Application Signal

Packaging Features

Packaging Method Package
Packaging Quantity 1

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.