




	1	2	3	4	5	6	7	8
A								
B								
C	27	33262311000012	FO Breakout Cable, MM, 2-channel, 50/125, OM3	100	±1%			
	26	33262310900012		90				
	25	33262310800012		80				
	24	33262310700012		70				
	23	33262310600012		60				
	22	33262310500012		50				
	21	33262310450012		45				
	20	33262310400012		40				
	19	33262310350012		35				
D	18	33262310300012		30				
	17	33262310250012		25				
	16	33262310200012		20				
	15	33262310150012		15				
	14	33262310140012		14				
	13	33262310130012		13				
	12	33262310120012		12				
E	11	33262310110012		11				
	10	33262310100012		10				
	9	33262310090012		9				
	8	33262310080012		8				
	7	33262310070012		7				
	6	33262310060012		6				
	5	33262310050012		5				
	4	33262310040012		4				
F	3	33262310030012		3				
	2	33262310020012		2				
	1	33262310010012		1	±15			
	Cont. no.	Part-no.	Type of cable	Dim. a[m]				
	1							



All rights reserved

Department HCS - RO

Created by

Inspected by

Standardisation


Date

State

Doc-Key / ECM-Nr.

Rev.

Page



All Dimensions in mm

Tech. Character.

Free size tol.

According to production drawing

HARTING Customised Solutions

D-32427 Minden

Title

Type

Number

PP XS LCdx Lg - PP XS LCdx Lg, MM Assy

TB

3326231XXX0012

100572207/UGD/033/D

500000127659

D

2/2