

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1210230467](#)  
**Status:** **Active**  
**Overview:** mPm DIN Valve Connectors  
**Description:** mPm DIN Valve Connector, Form C-Micro 9.4mm, PG7 Internal Threads, 3 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Flat Gasket and Screw, Bulk Pack Mounted



**Documents:**  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-121023-C19-001 \(PDF\)](#)

**General**  
Product Family Field Attachable / Accessories  
Series [121023](#)  
Form C - Micro 9.4mm  
IP Rating IP65, IP67  
Material - Contact Brass  
Overview [mPm DIN Valve Connectors](#)  
Product Name mPm  
Type Field Attachable Connector  
UPC 883906249090

**Physical**  
Cable Diameter N/A  
Coupling Type Internal Thread  
Diagnostics / LEDs No  
Diagnostics Port No  
Gender N/A  
Keyway None  
Material - Connector Body Polypropylene  
Material - Coupling Nut N/A  
Material - Plating Mating Silver  
Net Weight 10.886/g  
Orientation 90° Angle  
Pitch - Mating Interface 9.40mm  
Poles 3  
Temperature Range - Operating -40°C to +90°C  
Wire Size AWG N/A

**Electrical**  
Current - Maximum per Contact 16.0A  
Voltage - Maximum 250V AC / 300V DC

**Material Info**  
Engineering Number C19307N62

**Reference - Drawing Numbers**  
Packaging Specification PK-121023-C19-001  
Sales Drawing SD-121023-005-001

**EU ELV**  
**Not Relevant**

**EU RoHS** **China RoHS**  
**Compliant with**  
**Exemption 6(c)**  
**REACH SVHC**  
Contained Per -  
D(2021)4569-DC (8  
July 2021)  
Lead  
**Halogen-Free**  
**Status**  
**Low-Halogen**  
For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | 50 Image      |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**  
[121023 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION