


## STANDARD RECTANGULAR CONNECTORS



TE CONNECTIVITY (TE)  
**DMC-MD 24 A-K-S-T**  
DEUTSCH

DMC-MD 24 A-K-S-T  
TE Internal Number: ZPF000000000107607

Always EU RoHS/ELV Compliant

Product Type **Connector**

Connector Style **Receptacle**

Contact Plating Material **Gold Over Nickel**

✓ Active

Catalog Pages/Data Sheets

**DMC-M Series Single Module EN4165**

PDF

English

Please review product documents or [contact us](#) for the latest agency approval information.



Product Type Features

Product Type

**Connector**

Connector Style

**Receptacle**

Configuration Features

Keying

**A**

Contact Features

Contact Plating Material

**Gold Over Nickel**

Housing Features

Housing Material

**Composite**

Usage Conditions

Operating Temperature Range (°C)

**-55 – 175**

Product Compliance


[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

## CUSTOMERS ALSO BOUGHT

WIRE-TO-BOARD HEADERS & RECEPTACLES



HPI CONN., 2.0mm, R/A,  
SMT, 15P, 80u"  
1-1775469-5

Save to List

Find Similar Products

STANDARD RECTANGULAR CONNECTORS



DMC-MD 24 B-K-S-T  
DMC-MD 24 B-K-S-T

Save to List

Find Similar Products

MULTIPLE CONFIGURATION PCB CONNECTOR CONTACTS



MOD2 STIFT M A-PIN  
1-928776-7

Save to List

Find Similar Products

BOARD-TO-BOARD HEADERS & RECEPTACLES



2X32P HV100 REC  
CON.B/TE, 6.2, NO KINK  
3-829264-2

Save to List

Find Similar Products