



Industrial    Medical

# P1330FHF1MA00

Size (inch)	13.3"
Resolution	1920 × 1080
Temperature Range (°C)	-20 to 70
Viewing Angle (°)	88/88/88/88

[View all technical specifications](#)

**In Stock: 0**  
Multiple Distributors

[Order Now](#)

**Contact Tianma Sales**  
(408) 816-7029

In order to give you a personalized experience, this website (<https://usa.tianma.com>) uses cookies. You agree to allow us to use cookies by continuing to browse this site.

[Ok](#)    [Terms & Conditions](#)



# Tech Specs

**Part Number**

P1330FHF1MA00

**Target Market**

Industrial, Medical

**Size (inch)**

13.3"

**Resolution**

1920 x 1080

**Luminance (nits)**

1000

**Contrast Ratio**

1000:1

**Operating Temp. (°C)**

-20 to 70

**Interface**

LVDS

293.76 x 165.24



**Viewing Angle (°)**

88/88/88/88

**Display Mode**

SFT

**Resp. Time (ms)**

25

**Aspect Ratio**

16:9

**LED Driver**

No

**Touch Panel**

No

**Technology**

a-Si

**Resolution Name**

FHD

# Related Products



Industrial Medical Consumer



Industrial Medical Consumer



2.4"

TM024HDHP49-00

2.8"

TM028HDZP01-00



Products



solution tailored for your needs. **Let's create something amazing together!**

Contact Us

**Products**

P-Series

A-Series

Automotive

AMOLED

Advanced

**Our Industries**

**About Us**

**Support & Resources**

© 2026 Tianma America, Inc, All Rights Reserved  
Web Design by: Blacksmith Agency

**Representative Login**

**Terms & Conditions**

**Privacy Policy**

In order to give you a personalized experience, this website (<https://usa.tianma.com>) uses cookies. You agree to allow us to use cookies by continuing to browse this site.