



Part Number : [936000395](#)
Product Description : Heavy-Duty Plastic Gable Gland with Gasket and Nut, Pg9 Thread, Black RAL 9005
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Part Number : 7000.7830.6



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Plastic Gable Gland with Gasket and Nut, Pg9 Thread, Black RAL 9005
Cable Gland Type	IP68 with Nut and Gasket
IP Rating	IP68
Product Name	Heavy-Duty Connectors
Standard	DIN 40430, EN 60529
UPC	887191854977

Physical

Cable Diameter	4.00-8.00mm
Gland Color	Black RAL 9005
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Nut	Polyamide
Net Weight	8.000/g
Packaging Type	Bag
Panel Cutout Diameter	15.40mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +100°C
Thread Size	Pg9
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Sealed enclosures and boxes

This document was generated on May 09, 2026