

Search within category

GO

BUY NOW

DESIGN / INSTALL



CCH25-S10-C0

Fixed diameter cable clamp, heavy duty, #10 screw (M5), .25" (6.4mm) bundle, black, standard package.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Material	Weather Resistant Nylon 6.6			
Color	Black			
UL Recognized	E136577			
Diameter (In.)	0.20			
Diameter (mm)	5.1			
Width (In.)	0.50			
Height (mm)	6.3			
Length (mm)	11.7			
Width (mm)	12.7			
Bundle Offset (mm)	11.7			
Bundle Offset (In.)	0.46			
Environment	Outdoor			
Flammability Rating	UL94V-2			
Hole Diameter (In.)	0.20			
Hole Diameter (mm)	5.1			
Max. Bundle Diameter (In.)	0.25			
Max. Bundle Diameter (mm)	6.3			
Max. Continuous Use Temperature	-76°F - 185°F (-60°C - 85°C)			
Mounting Method	#10 (M5) Screw			
Type	Fixed Diameter Clamps - Screw Applied			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	100			

Yes, definitely.

No, I already find working with Panduit easy.