



Technical Data

27.12.2021

Heat shrinkable tubing up to 4:1 - 1 m lengths
TREDUX HA47 - thick wall adhesive lined

TREDUX-HA47-68/22

Article Number 321-50680



Material: Polyolefin, chemically cross-linked (PO-X)
Colour: Black (BK)
Adhesive: Hot melt adhesive

Supplied Ø D min.: 68.0 mm
Recov. Ø d max.: 22.0 mm
Wall (WT): 4.1 mm
Shrink Ratio: up to 4:1
Longitudinal Change After Shrinkage: -10% max.
Min. Shrink Temperature - °C: +120 °C

Flammability: not flame-retardant
Operating Temperature - °C: -55 °C to +110 °C

Dielectric Strength: 20 kV/mm
Tensile Strength: 14 MPa
Elongation at break: 400%(ASTM D 2671)



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved